

TUBE NECK OPTIONS



Tube Dia.	TUBE NECK OPTIONS									
13	 Standard T-13-1	 Bullet T-13-2	 Bullet (Blind) T-13-3	 Twist Off T-13-4						
16	 Standard T-16-1	 Bullet T-16-2	 Bullet (Blind) T-16-3	 Twist Off T-16-4	 Slant Tip T-16-5					
19	 Standard T-19-1	 Bullet T-19-2	 Bullet (Blind) T-19-3	 Twist Off T-19-4	 Twist Off T-19-5	 Slant Tip T-19-6	 Dome T-19-7			
22	 Standard T-22-1	 Bullet T-22-2	 Bullet (Blind) T-22-3	 Toothpaste T-22-4	 Twist Off T-22-5	 ABL T-22-6	 Small diameter T-22-7			
25	 Small diameter T-25-1	 Standard T-25-2	 Twist Off T-25-3	 Pump T-25-4	 Tip T-25-5	 Snap On T-25-6	 Bullet T-25-7			
30	 Standard T-30-1A/B	 Button T-30-2	 Long Neck T-30-3	 Large diameter T-30-4	 Pump T-30-5	 Tip T-30-6	 Snap On T-30-7	 Caulk Tip T-30-8		
35	 Standard T-35-1A/B	 Snap On T-35-2	 XR T-35-3A/B	 Squeeze pop T-35-4A/B/C	 Long neck T-35-5	 Large diameter T-35-6				
38	 Standard T-38-1	 Toothpaste T-38-2	 Button T-38-3	 Lube Nozzle T-38-4						
40	 Standard T-40-1A/B	 Standard	 Snap On T-40-2A/B	 Caulk Tip T-40-3	 Tip T-40-4	 Long Neck T-40-5	 Custom thread T-40-6	 Round Neck T-40-7	 Big theath T-40-8	 Lube Nozzle T-40-9
45	 Standard T-45-1	 XR T-45-2	 Long Neck T-45-3	 Snap On T-45-4						
49	 Standard T-49-1A/B									
50	 Standard T-50-1A/B	 Snap On T-50-2	 Snap On (Henkel) T-50-3	 Glue T-50-4	 Oil Line T-50-5	 Brush T-50-6				
55	 Standard T-55-1									
60	 Standard T-60-1									
OVAL	 30-Oval T-30-0	 30-Oval T-30-01	 30-Oval T-30-02	 35-Oval T-35-0	 40-Oval T-40-0	 50-Oval T-50-0	 Super Flat T-35-50			


13	Tube					Cap		
Tube No:	Photo	Thread Dia.(mm)	Orifice (mm)	Length Range (mm)		Photo	Cap No:	Cap Type
				Min	Max			
		φ8	φ2 or φ4	40	60		C-13-S-YD	Screw on Cap
		φ6	φ1.3	40	79		C-9-BS-SC	Ribbed Bullet Screw on CAP
		φ6	After cut the head , Orifice is Dia.1.5	40	79		C-9-BS-SC	Ribbed Bullet Screw on CAP
		/	After twist off the head , Orifice is Dia.3.2	40	79	/	/	/



16	Tube					Cap		
Tube No:	Photo	Thread Dia.(mm)	Orifice (mm)	Length Range (mm)		Photo	Cap No:	Cap Type
				Min	Max			
		φ8	φ2 /φ3	40	112		C-16-S-Y D	Screw on Cap
							C-15-RS-SC(XR)	Ribbed Screw on Cap
		φ6	φ1.3	40	120		C-9-B5-SC	Ribbed Bullet Screw on CAP
		φ6	After cut the head , Orifice is Dia.1.5	40	120		C-9-B5-SC	Ribbed Bullet Screw on CAP
		/	After twist off the head , Orifice is Dia.3.2	40	102	/	/	/
		φ12	φ1.5	40	128		C-15-S-FW	Lip balm cap





19	Tube					Cap		
Tube No:	Photo	Thread Dia.(mm)	Orifice (mm)□	Length Range (mm)□		Photo	Cap No:	Cap Type
				Min	Max			
		φ10	φ2 ~φ5	40	185		C-18-S-SC	Screw on Cap
						C-18-S-FW	Screw on Cap	
		φ5.2		C-14-RS-SC	Ribbed Screw On Cap			
				C-18-2L-FW	Double Wall Screw On Cap			
				C-18-H2L-FW	Tip Screw On Cap			
		φ6	φ1.3	40	120		C-9-BS-SC	Ribbed Bullet Screw on CAP
							C-18-HS-YD	Single Wall High Screw On Cap
		φ6	After cut the head , Orifice is Dia.1.5	40	120		C-9-BS-SC	Ribbed Bullet Screw on CAP
							C-18-HS-YD	Single Wall High Screw On Cap
							C-18-HS-YD	Aluminum Shell Screw On Cap
		/	After twist off the head , Orifice is Dia.3.2	40	140	/	/	/
		/	After twist off the head , Orifice is Dia.3.8	40	159	/	/	/
		φ14.6	φ1.5	40	125		C-18-S-FW	Lip balm cap
		φ14.8	φ1.3	40	127		C-18-RS-FW	Round balm cap

22	Tube					Cap		
Tube No:	Photo	Thread Dia.(mm)	Orifice (mm)	Length Range (mm)		Photo	Cap No:	Cap Type
				Min	Max			
22 ₁		φ10.6	φ2 ~φ5	40	145		C-22-S-SC	Screw on Cap
22 ₂		φ6	φ1.3	40	129		C-9-BS-SC	Ribbed Bullet Screw on CAP
							C-21-HS-FW	Single Wall High Screw On Cap
22 ₃		φ6	After cut the head , Orifice is Dia.1.3	40	129		C-9-BS-SC	Ribbed Bullet Screw on CAP
							C-21-HS-FW	Single Wall High Screw On Cap
22 ₄		φ12.8	φ7.5	40	145		C-15-TF-CT	Toothpaste Flip Top Cap
22 ₅		/	After twist off the head , Orifice is Dia.3.2	40	140	/	/	/
22 ₆		φ5.9	φ2	40	150		C-20-S-SC	ABL Tube Screw on cap
22 ₇		φ10	φ2 ~φ5	40	145		C-22-S-YD	Screw on Cap
							C-22-AS-YD	Aluminum Shell Screw On Cap
			φ5.2				C-18-2L-FW	Double Wall Screw On Cap




25	Tube					Cap		
Tube No:	Photo	Thread Dia.(mm)	Orifice (mm)	Length Range (mm)		Photo	Cap No:	Cap Type
				Min	Max			
25 ₁		φ10	φ5.2	40	150		C-18-2L-FW	Double Wall Screw On Cap
			φ2 ~φ5				C-25-S-YD	Screw on Cap
							C-14-SR-SC	Screw on Ribbed Cap
25 ₂		φ10.8	φ2 ~φ5	40	150		C-25-S-SC	Screw on Cap
							C-25-iF-SC	Flip Top Cap(Orifice= 2.5mm)
							C-25-nF-SC	Flip Top Cap(Orifice= 2.5/4mm)
							C-25-iF-HH	Matte Flip Top Cap (Orifice= 2.5mm)
							C-25-AS-SC	Aluminum Shell Screw On Cap
							C-25-RS-SC	Ribbed Screw on Cap
25 ₃		/	After twist off the head , Orifice is Dia.3.2	40	162	/	/	/
25 ₄		φ17.5	φ9.3	40	155		C-25-PC-YW	Airless Pump
25 ₅		φ7.8	After cut the head , Orifice is Dia.2.0	40	160		C-25-HS-SC	High Screw On Cap
25 ₆		φ14.9	φ7.8	40	150		C-25-SOF-SC	Snap On Flip Top Cap (Orifice=2/2.5/3mm)
25 ₇		φ6	φ1.3	40			C-9-BS-SC	Ribbed Bullet Screw on CAP

30	Tube					Cap		
	Photo	Thread Dia.(mm)	Orifice (mm)	Length Range (mm)		Photo	Cap No:	Cap Type
				Min	Max			
30		φ14.5	φ2~φ8	50	170		C-18-RS-SC	Ribbed Screw on cap
							C-28-S-YY/FW	Screw on cap
							C-28-AS-YY	Aluminum Shell Screw On Cap
							C-28-RS-SC	Ribbed Screw on cap
							C-28-MS-YD	Matte Screw on cap
							C-30-IF-YD	Flip Top Cap (Orifice= 3/5mm)
							C-30-IF-FW	Flip Top Cap (Orifice= 3mm)
							C-30-MF-HH	Matte Flip Top Cap (Orifice= 3.5/5mm)
							C-27-LS-SC	Long mouth Screw on cap+ small cap
30		φ10.5	φ5~φ6	50	170		C-18-nF-SC	Button Flip Top Cap(Orifice= 5mm)
			φ3.5				C-18-RS-SC	Button Screw On Cap
30		φ14.2	φ2~φ5	50	153		C-30-HS-YY	High Screw On Cap
30		φ23.6	φ18	50	168		C-30-RF-SC	Ribbed Flip Top Cap (Orifice= 3mm)
30		φ17.5	φ9.3	50	155		C-25-PC-YW	Airless Pump
30		φ9.8	After cut the head , Orifice is Dia.2.0	50	155		C-30-HS-SC	High Screw On Cap
30		φ17.9	φ9.7	50	170		C-30-SOF-SC	Snap On Flip Top Cap (Orifice=2/2.5/3/4/5mm)
30		/	After cut the head , Orifice is Dia.3.5	50	200		C-13-SI-SC	Pagoda Cap


35	Tube					Cap		
Tube No:	Photo	Thread Dia.(mm)	Orifice (mm)	Length Range (mm)		Photo	Cap No:	Cap Type
				Min	Max			
	 	φ14.5	φ2~φ8	50	180		C-35-RS-SC	Ribbed Screw on cap
							C-35-S-SC	Matte & Glossy Screw on cap
							C-35-S-FW	Screw on cap
							C-35-IF-YY	Flip Top Cap (Orifice= 3/5mm)
							C-35-RMF-YD	Round Matte Flip Top Cap (Orifice= 3.5/5mm)
							C-35-RMF-HH	Round Matte Flip Top Cap (Orifice= 3.5/5mm)
							C-35-S-SC	Aluminum Shell Screw On Cap
		φ21.2	φ9.7	50	193		C-35-SOF-SC	Snap On Flip Top Cap (Orifice= 3/5mm)
		φ14.09	φ2~φ8	50	164		C-35-XR-SC	Flip Top Cap (Orifice= 3.18/6.35/8.13mm)
							C-35-S-SC	Screw on cap
		φ26.5	φ3	50	160		C-35-SC-SC	Safety Cap
		φ13.5	φ2~φ5	50	165		C-35-HS-YY	High Screw on cap
		φ27.38	φ21.6	50	168		C-35-RF-SC	Ribbed Flip Top Cap (Orifice= 3mm)




38	Tube					Cap		
Tube No:	Photo	Thread Dia.(mm)	Orifice (mm)	Length Range (mm)		Photo	Cap No:	Cap Type
				Min	Max			
38 ₁		φ14.5	φ2~φ8	50	180		C-18-RS-SC	Ribbed Screw on cap
							C-37-RS-SC	Ribbed Screw on cap
							C-37-nF-HH	Flip Top Cap (Orifice= 5.5mm)
							C-38-iF-YY	Flip Top Cap (Orifice= 2.5/3/5/6mm)
							C-37-MiF-SC	Matte Flip Top Cap (Orifice= 3/5mm)
							C-27-LS-SC	Long mouth Screw on cap+ small cap
38 ₂		φ12.8	φ7.5	50	182		C-15-TF-CT	Toothpaste Flip Top Cap
38 ₃		φ10.5	φ5~φ6	50	160		C-18-nF-SC	Button Flip Top Cap(Orifice= 5mm)
			φ3.5				C-18-RS-SC	Button Screw On Cap
38 ₄		φ14.2	φ4	50	210		C-19-RS-SC	Nozzle Ribbed Screw on cap

40	Tube					Cap		
Tube No:	Photo	Thread Dia.(mm)	Orifice (mm)	Length Range (mm)		Photo	Cap No:	Cap Type
				Min	Max			
40 ₁₈₈		φ14.5	φ2~φ8	50	197		C-38-RnF-HH	Round Flip Top Cap (Orifice3.18/5/6.3 5/8.13mm)
						C-38-MiF-HH	Matte Flip Top Cap (Orifice3.5/5.0mm)	
						C-38-iF-YY	Flip Top Cap (Orifice3/5/6mm)	
						C-38-iF-SC	Matte & Glossy Flip Top Cap (Orifice3/5/6mm)	
						C-38-RS-YD	Ribbed Screw on cap	
						C-38-S-FW	Screw on cap	
						C-38-S-SC	Screw on cap	
						C-38-RS-SC	Ribbed Screw on cap	
40 ₂₈₈		φ21.3	φ9.7	50	190		C-38-SF-SC	Matte & Glossy Snap On Flip Top Cap(Orifice2/3/5 mm)
40 ₃		/	After cut the head ,Orifice is Dia.3.5	50	205		C-13-Si-SC	Pagoda Cap
40 ₄		φ12.8	After cut the head ,Orifice is Dia.3.2	50	160		C-39-HS-SC	High Screw On Cap
40 ₅		φ13.5	φ2~φ8	50	162		C-38-HS-SC/FW	High Screw On Cap
40 ₆		φ14.2	φ7.4	50	190		C-39-Nos-SC	nozzle and outer cap
40 ₇		φ32	φ2.8	50	180		C-35-MS-SC	Matte Screw on cap
40 ₈		φ21.5	φ2~φ15	50	190		C-38-nF-HH	Matte & Glossy Flip Top Cap (Orifice3.5/4.75/6.5mm)
40 ₉		φ14.2	φ4	50	206		C-19-RS-SC	Nozzle Ribbed Screw on cap

45	Tube					Cap		
Tube No:	Photo	Thread Dia.(mm)	Orifice (mm)	Length Range (mm)		Photo	Cap No:	Cap Type
				Min	Max			
45₁		φ14.5	φ2~φ8	50	195		C-38-iF-YY	Flip Top Cap (Orifice3/5/6mm)
45₂		φ21.5	φ2~φ15	50	200		C-43-S-FW	Screw on cap
							C-44-iF-YY	Flip Top Cap (Orifice5mm)
							C-44-iF-HH	Flip Top Cap (Orifice3.5/5/6.35 mm)
45₃		φ15	φ2~φ8	50	152		C-44-HS-SC	High Screw on cap
45₄		φ21.3	φ11.8	50	190		C-44-iF-YY	Flip Top Cap (Orifice5mm)



49	Tube					Cap		
Tube No:	Photo	Thread Dia.(mm)	Orifice (mm)	Length Range (mm)		Photo	Cap No:	Cap Type
				Min	Max			
49_{1A}		φ21.5	φ2~φ15	50	200		C-48-iF-YY	Flip Top Cap (Orifice3/5/6mm)
49_{1B}		φ21.5	φ8.38~φ8.76	50	184		C-48-nF-XR	Matte & Glossy Flip Top Cap (Orifice3.18/5/6.35/8.13mm)



50		Tube				Cap		
Tube No:	Photo	Thread Dia.(mm)	Orifice (mm)	Length Range (mm)		Photo	Cap No:	Cap Type
				Min	Max			
50 ₁		φ21.5	φ2~φ15	50	188/230		C-48-RnF-HH	Round Flip Top Cap(Orifice3.5/5 mm)
							C-48-iF-HH	Flip Top Cap(Orifice3.5/5 mm)
							C-48-nF-XR	Matte & Glossy Flip Top Cap (Orifice3.175/5/6.35/8.13mm)
							C-48-iF-YY	Flip Top Cap(Orifice3/5/6 mm)
							C-48-S-YY	Matte & Glossy Screw on cap
							C-37-iF-HH	Matte & Glossy Flip Top Cap (Orifice3.5/4.76/6.5mm)
50 ₂		φ21.3	φ10	50	193		C-48-iF-SC/HH	Matte & Glossy Snap On Flip Top Cap(Orifice2/3/5 mm)
50 ₃		φ21.5	φ11.8	50	215		C-48-iF-HH	Snap On Flip Top (Orifice3.5/4.76/6.5mm)
50 ₄		φ23.5	φ17.5	50	179		C-48-Ci-SC/XR	Cover and inner Cap
50 ₅		φ14.2	After cut the head , Orifice is Dia.3.6	50	206		C-48-RS-SC	Ribbed Screw On Cap
50 ₆		φ41.8	φ8	50	185		C-48-BC-	Brush cover
								

55	Tube					Cap		
Tube No:	Photo	Thread Dia.(mm)	Orifice (mm)	Length Range (mm)		Photo	Cap No:	Cap Type
				Min	Max			
		φ21.5	φ2~φ15	50	200		C-52-IF-HH	Flip Top Cap (Orifice=5mm)

60	Tube					Cap		
Tube No:	Photo	Thread Dia.(mm)	Orifice (mm)	Length Range (mm)		Photo	Cap No:	Cap Type
				Min	Max			
		φ21.5	φ2~φ15	50	200		C-57-IF-HH	Flip Top Cap (Orifice=3.5/6mm)

Oval	Tube					Cap		
Tube No:	Photo	Thread Dia.(mm)	Orifice (mm)	Length Range (mm)		Photo	Cap No:	Cap Type
				Min	Max			
		φ14	φ2~φ6	50	179		C-30-OS-SS	Oval screw on cap
		φ12.5	φ6				C-30-OF-HH	Oval Flip Top Cap (Orifice=2/3.5mm)
		φ12.0	φ2/3/4/5				C-30-S-SC	Oval screw on cap
		φ12.5	φ6	50	175		C-35-OF-HH	Oval Flip Top Cap (Orifice=2/3/4mm)
			φ2~φ6				C-35-OS-SC	Oval screw on cap
		φ16	φ6	50	189		C-40-OF-HH	Oval Flip Top Cap (Orifice=2/3/5mm)
			φ2~φ6				C-40-OS-HH	Oval screw on cap
		φ21	φ10	50	170		C-50-OF-HH	Oval Flip Top Cap (Orifice=2/5mm)
		φ10.5	φ4	50	167		C-35-SS-SC	Super Flat Screw On Cap